



LET'S GET BACK TO CLEAN AIR

The back pack vacuum with HEPA filtration.

We've got your back when it comes to clean air

This vacuum allows the operator to move around quickly and easily allowing for maximum productivity. To take full advantage of this productivity, we have fitted the Vac Pac HEPA with a lightweight, ergonomic backpack harness for hours of pain-free operation. The standard HEPA-level filter ensures that this vac is leaving the air in your facility clean and healthy. Clean quietly without worrying about being a noisy distraction. Operating at a mere 67 dBA, this powerful vacuum is quiet, making it perfect for daytime cleaning.



Meets your needs

- HEPA filtration is now standard, providing optimum air quality by filtering with 99.9% effectiveness to 0.3 microns,
- Powerful 1.7 hp motor vacuums with authority
- A kit of most-used vacuum tools comes standard with the machine
- The Vac Pac HEPA is constructed of tough molded polyethylene to ensure it can handle daily use

Flexible

- Vacuum hose is a top-mounted swivel design for left-hand and right-hand operation
- The Vac Pac HEPA is available in six and ten quart capacities to accommodate different operators and job requirements

Productive

- Light weight and comfortable harness system makes the job easier
- Vacuum Power Switch is mounted on the hip within easy view and reach of the operator
- Padded hip and shoulder harness increases vacuum operators comfort
- Harness has a chest strap for better weight distribution and operator comfort
- Powerful 1.7 hp motor vacuums with authority
- Quiet vacuum operation is perfect for daytime cleaning

Technical Specifications and Order Numbers.

		Vac Pac HEPA 6	Vac Pac HEPA 10
TECHNICAL SPECIFICATIONS			
Vacuum motor	HP	1.7	1.7
Air flow	cfm	112	112
Filter bag capacity	qt	6	6
Vacuum hose	ft x in	5 x 1.5	5 x 1.5
Operating noise level	dBA	67	67
Weight	lbs	10	11
Dimensions (L x W x H)	in	8.5 x 8.8 x 19.8	8.5 x 8.8 x 23.7
Waterlift	in	104	104

EQUIPMENT

Order No.	Item Description
1.014-013.0	Vac Pac HEPA Back Vacuum, 6 qt. (Includes hose and tool kit)
1.014-014.0	Vac Pac HEPA Back Vacuum, 10 qt. (Includes hose and tool kit)

ACCESSORIES

Order No.	Item Description
■ 8.628-666.0	Wand, 2 PC Aluminum Double Curve
■ 8.619-894.0	Hose Assembly
■ 8.639-285.0	HEPA pleated filter (standard on HEPA models)
■ 8.619-884.0	Filter Bag Liner, Cloth VP10
■ 8.619-885.0	Filter Bag, VP10 Paper Pkg/10
■ 8.619-887.0	Filter Dome
■ 8.604-141.0	Tool Kit, back-pack vacuum (includes 5 items below)
■ 8.628-451.0	Crevice Tool
■ 8.600-008.0	5" Upholstery Tool
■ 8.628-360.0	Upholstery Brush
■ 8.600-007.0	3" Dusting Tool
■ 8.600-009.0	Tube, 20" Extension
□ 8.609-022.0	Spotter Wand (for use with 8.606-312.0 & 8.603-302.0)
□ 8.606-312.0	Tool, Spot Lite (requires 8.609-022.0)
□ 8.603-302.0	Tool, Quick Sweep
□ 8.604-143.0	Vac Pac Overhead Kit
□ 9.840-611.0	Air Turbine Tool with Wand
□ 8.604-142.0	Vac Pac Floor Pick-Up Kit
□ 8.604-144.0	Vac Pac SpotLite Kit
□ 8.604-145.0	Vac Quick Sweep
□ 8.628-332.0	Air Turbine Tool
□ 8.628-454.0	Tool, Smooth Sweep
□ 8.628-463.0	Wand, 1 PC Chrome Steel Single Curve
□ 8.628-451.0	Tool, 28" Plastic Crevice
□ 8.628-445.0	Tool, Carpet
□ 8.628-444.0	Tool, Bristle Shod Dry Pick-Up
□ 8.604-141.0	Vac Pac Tool Kit (#02293 crevice tool, #02083 dusting brush, #02084 upholstery tool, #02085 upholstery tool brush, #02086 extension tube)
□ 9.840-632.0	Vac Pac 2-Piece Aluminum Wand
□ 8.619-876.0	Vac Pac Crevice Tool
□ 8.639-285.0	For Vac Pac HEPA 6 & 10
□ 8.619-885.0	For Vac Pac HEPA 10, package of 10
□ 8.619-884.0	For Vac Pac HEPA 10
□ 8.631-254.0	For Vac Pac HEPA 6 and Vac Pac HEPA 10
□ 8.619-891.0	For Vac Pac HEPA 6
□ 8.619-890.0	For Vac Pac HEPA 6

■ Included with all machines □ Optional for all machines ♦ Included with some machines

Please contact us for more information:

North America

4555 Airport Way
Denver, CO 80239 U.S.A.

Phone +1 800 444-7654
Fax +1 866 271-0520

Canada

6535 Millcreek Drive
Unit 67
Mississauga, ON L5N 2M2 Canada

Phone +1 905 672-8233
Fax +1 905 672-3155

www.windsorkarchergroup.com